

Rittal – The System.

Faster – better – everywhere.



HD 4000.250 Levelling feet HD

State: 23/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.250 - Levelling feet HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

Features

Model No.	HD 4000.250
Design	with base attachment
Benefits	Minimises cleaning time thanks to fully covered, permanently sealed threads Compensation of floor inclines up to an angle of 10° thanks to flexible base Baying can even be achieved on sloping floors, thanks to a large levelling range Certification to 3-A Sanitary Standards
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	Assembly parts and seals
Load capacity	Max. 7000 N static per levelling foot
Dimensions	Thread: M12
To fit	Enclosure type: HD compact enclosure VX VX SE TS
Levelling range	122 - 175 mm
Packs of	4 pc(s).
Net weight	2.4 kg
Gross weight	2.5 kg
Customs tariff number	73181900
ETIM 9	EC002622
ETIM 8	EC002622
ECLASS 8.0	27189263

Features

Product description

HD Levelling foot, with base mount, Stainless steel 1.4301