

Rittal – The System.

Faster – better – everywhere.



AS 4051.191

Wire Terminal WT L fully automated wire processing machine

State: 15/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.191 - Wire Terminal WT L fully automated wire processing machine

The Wire Terminal WT L5 B fully automated wire processing machine can process wire cross-sections ranging from 0.5–2.5 mm². This includes length-cutting, insulation-stripping, crimping and project-specific labelling of the wires. The finished wires are output in chain bundles on an order-specific basis. Alternatively, the wire output is also available as an ejection system.



Features

| | |
|---------------------|---|
| Model No. | AS 4051.191 |
| Design | Wire Terminal WT L5 B (wire chain bundler) |
| Product description | The Wire Terminal WT L5 B fully automated wire processing machine can process wire cross-sections ranging from 0.5–2.5 mm ² . This includes length-cutting, insulation-stripping, crimping and project-specific labelling of the wires. The finished wires are output in chain bundles on an order-specific basis. Alternatively, the wire output is also available as an ejection system. |
| Benefits | <ul style="list-style-type: none">Boost efficiency with the option of production in sorted chain bundlesThe bundled batch may be removed during active productionSupports the wiring process at various locationsSimplifies the wiring process with step-by-step instructions in Eplan Smart Wiring |

Features

| | |
|--------------------------|---|
| Technical specifications | <p>5 wire end ferrule infeeds via feeder bowls</p> <p>Crimping range 0.5 mm²: Crimping length 8 mm (0.31 in.) and 10 mm (0.39 in.)</p> <p>Crimping range 0.75 mm²: Crimping length 8 mm (0.31 in.), 10 mm (0.39 in.) and 12 mm (0.47 in.)</p> <p>Crimping range 1 mm²: Crimping length 8 mm (0.31 in.), 10 mm (0.39 in.) and 12 mm (0.47 in.)</p> <p>Crimping range 1.5 mm²: Crimping length 8 mm (0.31 in.), 10 mm (0.39 in.), 12 mm (0.47 in.) und 18 mm (0.71 in.)</p> <p>Crimping range 2.5 mm²: Crimping length 8 mm (0.31 in.), 12 mm (0.47 in.) and 18 mm (0.71 in.)</p> <p>The Wire Terminal WT L can process wire lengths from 150 mm to 10 m</p> <p>Wire output as chain bundle</p> <p>The WT L Wire Terminal can accommodate one wire infeed block.</p> |
| Supply includes | <p>Machine frame and encapsulation</p> <p>Operating unit</p> <p>1 x WT 16 vibratory bowl feeder for 0.5 mm²</p> <p>2 x WT 20 vibratory bowl feeders for 0.75/1.0 mm²</p> <p>2 x WT 29 vibratory bowl feeders for 1.5/2.5 mm²</p> <p>Chain bundle module WT</p> <p>10 reels of WT bundle tape, 50 m each</p> |
| Machinable material | <p>Fine-wire copper cables to EN 60228 / VDE 0295 Category 5</p> <p>Wire end ferrules with plastic collar to DIN 46228-4 and Multinorm</p> |
| Note | <p>Please talk to your Rittal sales consultant about a bespoke machine configuration.</p> <p>German and English are included as standard with the Wire Terminal</p> <p>The vibratory bowl feeders and the separation of single wire end ferrules are designed for the dimensional tolerances of Rittal wire end ferrules to DIN 46228-4:2019-02. If the wire end ferrules used exceed the defined dimension tolerances, it may be necessary to design/test a new bowl feeder and to adapt the wire end ferrule separation.</p> <p>We reserve the right to make technical modifications</p> |
| Machine options | <p>Wire store WT Tube 12 (4051.218)</p> <p>WT printer IQ.JET, black 4051281</p> <p>WT printer IQ.JET, white 4051280</p> |

Features

| | |
|-----------------------------|---|
| Interfaces | Eplan Pro Panel Eplan Smart Wiring |
| Compressed air supply min. | 5.5 bar |
| Compressed air supply max. | 6 bar |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Control voltage (DC) | 24 V |
| Power consumption (approx.) | 1 kW |
| Cycle time | 11 s |
| Wires per hour approx. | 320 |
| Support area | Width: 2,170 mm Height: 1,870 mm Depth: 1,080 mm |
| Customs tariff number | 84633000 |
| ETIM 8 | EC000000 |
| ECLASS 8.0 | 18129090 |
| Product description | Wire Terminal WT L5 W fully automated wire processing machine (wire chain bundler) |