

Rittal – The System.

Faster – better – everywhere.



SK 3342.024

Rack-mounted fans for 482.6 mm (19")

State: 22/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3342.024 - Rack-mounted fans for 482.6 mm (19") Air throughput 320 – 480 m³/h

Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots.

Features

| | |
|-------------------------------------|--|
| Model No. | SK 3342.024 |
| Product description | Rack-mounted fan for direct installation in the 482.6 mm (19") level. Installation allows air to circulate permanently inside the enclosure, thus preventing the formation of hot spots. |
| Colour | RAL 7035 |
| Supply includes | Fully wired unit ready for connection Terminal strip and assembly parts |
| Air throughput (unimpeded air flow) | 480 m ³ /h |
| Note on Model No. | Extended delivery times. |
| Rated operating voltage | 24 V (DC) |
| Rated current max. | With DC: 0.74 A |
| Pre-fuse | Miniature circuit-breaker/fuse: 6 A |
| Dimensions | Width: 482.6 mm Height: 44 mm Depth: 200 mm |
| Distance between axes of fans | 105 mm |
| No. of fans | 3 |
| Noise level | With DC: 51 dB(A) |
| Operating temperature range | -10 °C...55 °C |
| Packs of | 1 pc(s). |
| Net weight | 1.75 kg |
| Gross weight | 1.86 kg |

Features

| | |
|-----------------------|---|
| Customs tariff number | 84145915 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | SK rack-mounted fan, for 482.6 mm (19"), 480 m ³ /h, 24 V (DC), WHD: 482.6 x 44 x 200 mm |

Approvals

| | |
|--------------|-------------------------------|
| Approvals | UR + C-UR (recognized) VDE |
| Explanations | Declaration of conformity |