

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.030 Flex crimping tool

State: 2/6/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.030 - Flex crimping tool for wire end ferrules

For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.



## Features

Model No.	AS 4054.030
Design	Straight
Product description	For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.
Benefits	Front or side accommodation of the wire end ferrule with a rotatable head Minimal effort required with large wire cross-sections Uniformly high quality compression Releasable ratchet Self-adjusting
Material	High-quality special tool steel
Surface finish	Coated, black, matt
Colour	Handle: Anthracite and Rittal Power Pink
Compression	Trapezoid crimp
Direction of cable entry	front and side
Dimensions	Length: 180 mm
AWG	26 - 8
For cross-section	0.14 - 10 mm <sup>2</sup>
Packs of	1 pc(s).

# Features

---

Net weight	0.35 kg
Gross weight	0.388 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811
Product description	AS crimping tool for cross-section 0.14 – 10 mm <sup>2</sup> , rotating head, trapezoidal crimp