

Rittal – The System.

Faster – better – everywhere.



AS 4055.481 Hole punch set, PG

State: 4/8/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.481 - Hole punch set, PG for sheet steel

For punching round cut-outs

Features

| | |
|--|--|
| Model No. | AS 4055.481 |
| Design | With 3 cutting points |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | 5 female dies 5 male dies 2 tension screws with ball bearing Ø 9.5 x 50 mm HSS pilot drill Ø 11 mm 1 tube of lubricant paste Plastic case |
| Machinable material | Sheet steel |
| Maximum machinable material thickness, sheet steel | 2 mm |
| Ø punch | 15.2 mm 18.6 mm 20.4 mm 22.5 mm 28.3 mm |
| Note | When operating with wrenches, tension screws with ball bearings should be used. |
| Suitable for hydraulic bolt order number | 4055.661 |
| Packs of | 1 pc(s). |
| Net weight | 0.909 |
| Gross weight | 0.91 |
| Customs tariff number | 82051000 |
| EAN | 4028177808614 |

Features

| | |
|------------|----------|
| ETIM 9 | EC002121 |
| ETIM 8 | EC002121 |
| ECLASS 8.0 | 21049047 |