


Rittal – The System.

Faster – better – everywhere.



TS 4162.000

Threaded blocks

State: 31/1/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4162.000 - Threaded blocks

Used on enclosures and rails with rectangular system punching 12.5 x 10.5 mm with snap-off insertion aid, die-cast zinc.



Features

Model No.	TS 4162.000
Product description	With snap-off insertion aid, die-cast zinc.
Installation options	<p>On the horizontal and vertical VX enclosure section</p> <p>On the vertical TS, VX SE enclosure section via adaptor rails for VX compatibility</p> <p>On the horizontal TS enclosure section</p> <p>On the horizontal VX SE enclosure section, bottom</p> <p>On the horizontal VX SE enclosure section, top in the depth</p> <p>On punched rails 23 x 23 mm</p> <p>On punched section without mounting flange, 23 x 73 mm</p> <p>On punched section without mounting flange, 45 x 88 mm</p> <p>On punched sections with mounting flanges, 23 x 64 mm</p> <p>On punched sections with mounting flanges, 23 x 73 mm</p> <p>On punched sections with mounting flanges, 23 x 89 mm, stainless steel</p> <p>On enclosures and rails with rectangular system punching 12.5 x 10.5 mm.</p>
Dimensions	Thread: M6
To fit enclosure type	VX TS VX SE
Thread	M6

Features

Packs of	50 pc(s).
Net weight	0.45
Gross weight	0.5
Customs tariff number	73181692
EAN	4028177092945
ETIM 9	EC002358
ETIM 8	EC002358
ECLASS 8.0	23110815