

Rittal – The System.

Faster – better – everywhere.



SV 3458.500

Conductor connection clamp

State: 15/8/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3458.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3458.500
Product description	For connecting round conductors and laminated copper bars.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	16.5 x 15 mm
Note	Wire end ferrules should be used with fine wire conductors
Connection of round conductors	35 - 70 mm ²
For bar thickness	10 mm
Packs of	15 pc(s).
Net weight	1.65
Gross weight	1.679
PCF per pack (cradle-to-gate)	6.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
EAN	4028177042766
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

SV conductor connection clamps
for E-CU busbars and Rittal PLS.
For bar thickness: 10 mm
Connection of round conductors 35 - 70 mm²
Wire end ferrules should be used with
fine wire conductors.
Clamping area: for laminated copper bars 15 mm
Tightening torque
Conductor connection clamp: 10 - 12 Nm
Material: sheet steel, zinc plated, passivated