

Rittal – The System.

Faster – better – everywhere.



SZ 4000.058

Attachable sloped roof

State: 31/7/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4000.058 - Attachable sloped roof for VX

For retrofitting individual or bayed VX25 enclosures made from spray-finished sheet steel, with the maximum possible opening to the adjacent roof at the baying point.



Features

| | |
|-------------------------------------|---|
| Model No. | SZ 4000.058 |
| Technical specifications | Roof projection, front: 8 mm |
| Material | Sheet steel |
| Surface finish | powder-coated |
| Colour | RAL 7035 |
| Supply includes | Assembly parts and seals |
| Dimensions | Height, front: 35 mm |
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Note on Model No. | Please quote the complete design code on all enquiries and orders. Extended delivery times. |

Features

| | |
|--------------------|--|
| Design code number | Roof tilt: 1 = 30° (EHEDG standard) or 2 = 45° Enclosure width: ... mm (max. 1200 mm) Enclosure depth: ... mm 1 = for VX free-standing enclosure 2 = for bayed VX end enclosure, left (with T-section seal and connection accessories) 3 = for bayed VX end enclosure, right (with T-section seal and connection accessories) 4 = for bayed VX enclosure, centre (with T-section seal and connection accessories) Example: 1 - 800 - 600 - 1 (sloped attachment with 30° roof pitch - width 800 mm - depth 600 mm - for VX free-standing enclosure) |
| Packs of | 1 pc(s). |
| Net weight | 2 |
| Gross weight | 2.1 |
| EAN | 4028177937130 |