

Rittal – The System.

Faster – better – everywhere.



CP 6148.000 Twin castors

State: 6/6/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6148.000 - Twin castors

For mobile use, for mounting directly on the enclosure.

Features

Model No.	CP 6148.000
Product description	For mobile use, for mounting directly on the enclosure.
Colour	Black with grey running surface
Supply includes	4 twin castors, 2 x with, 2 x without locks Assembly parts
To fit	Enclosure type: VX Enclosure type: VX IT Enclosure type: TS Enclosure type: TS IT Enclosure type: VX SE Enclosure type: PC Enclosure type: TP pedestals Enclosure type: IW Enclosure type: Data Rack Enclosure type: Chiller
Clearance floor	85 mm
Max. load capacity (static) per component	750 N
To fit Model No.	6106.200 6106.300
Dimensions	Thread: M12 x 20
Packs of	1 pc(s).
Net weight	1.115 kg
Gross weight	1.293 kg
Customs tariff number	39269097
ETIM 9	EC002621
ECLASS 8.0	27189262

Features

Product description

CP Twin castors, 2 each with/without lock, static load per castor 75 kg