

# Rittal – The System.

Faster – better – everywhere.



## CP 6206.460

## Tilting adaptor $+100^{\circ}/-60^{\circ}$

State: 31/7/2025 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6206.460 - Tilting adaptor +100°/–60° for support arm connection 120 x 65 mm

For mounting on IW worktop, prepared for attachment Ø 130 mm, surfaces or attachments/couplings with support arm connection 120 x 65 mm. To fit enclosures up to 20 kg with support arm connection. With cable tube for protected cable entry.

## Features

Model No.	CP 6206.460
Design	For mounting on IW worktop, prepared for attachment of 130 mm diameter Surfaces Attachment/coupling with support arm connection 120 x 65 mm To fit enclosures up to 20 kg with support arm connection 90 x 71 mm Ø 130 mm 120 x 65 mm VESA Standard 75 With cable tube for protected cable entry
Product description	Tilting angle adjustable in 7.2° increments via clamping lever and may be limited to +100°/–15° using the stop screw supplied loose.
Material	Tilting adaptor: Sheet steel, spray-finished Concertina section: Plastic
Colour	Tilting adaptor: RAL 7035 Concertina section: RAL 7024
Supply includes	Assembly parts Concertina section
Rotating/tilting	Yes
Tilt angle note	Adjustable in 7.2° increments via clamping lever and may be limited to +100°/–15° using the stop screw supplied loose
Packs of	1 pc(s).
Net weight	0.86
Gross weight	0.871

# Features

PCF per pack (cradle-to-gate)	3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177684454
ETIM 9	EC000882
ECLASS 8.0	27400556

# Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------