Rittal – The System.

Faster – better – everywhere.







AS 4055.222 Hole punch, round

State: 8/12/2025 (Source: rittal.com/in-en)



AS 4055.222 - Hole punch, round for sheet steel

For punching round cut-outs

Features

Model No.	AS 4055.222
Design	With 3 cutting points
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies Tension screw without ball bearing
Machinable material	Sheet steel
Maximum machinable material thickness, sheet steel	2 mm
Ø punch	22.5 mm
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.661
Tension screw (Ø x L)	9.5 x 50 mm
Hydraulic tension screw Ø	9.5 mm 19 mm
Packs of	1 pc(s).
Net weight	0.113
Gross weight	0.133
Customs tariff number	82073010
EAN	4028177808232
ETIM 9	EC000156

© Rittal 2025

Features

ETIM 8	EC000156	
ECLASS 8.0	21049047	

© Rittal 2025 3