

# Rittal – The System.

Faster – better – everywhere.



## DK 7856.110

## PSM socket modules

State: 9/6/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7856.110 - PSM socket modules

The various modules may be inserted into the support rail in any combination.

## Features

Model No.	DK 7856.110
Design	non-switchable
Product description	The modular system facilitates basic configuration of the racks, thanks to a vertical support rail with single-/3-phase infeed. The various socket modules to supply the active components may be snap-fitted into the support rail. The various modules, earthing pins, IEC320 etc. may be inserted into the support rail in any combination. This is easily achieved, even by non-electricians, thanks to the shock hazard protected plug & play system.
Material	Section: Aluminium, anodised Socket inserts: Plastic (PA6 GF 30 V1)
Length	250 mm
Type of electrical connection	WAGO WINSTA MIDI
Phases per infeed	1~
Thermal overcurrent protection	per socket module
Rated operating voltage	110 V – 230 V AC, 50/60 Hz
Rated current (max.)	16 A
Required number of module slots	1
Dimensions	Length: 250 mm
Operating temperature range	5 °C...45 °C
Ambient humidity (non-condensing)	5...95 %
Sockets	4 x F/B (type E, CEE 7/5)
Packs of	1 pc(s).
Net weight	0.34

# Features

Gross weight	0.36
Customs tariff number	85369001
EAN	4028177402560
ETIM 9	EC000330
ECLASS 8.0	27142604

# Approvals

Explanations	Declaration of conformity
--------------	---------------------------

# Tender text

Power system module plug-in module, France / Belgium 4  
x with 16 A fuse

Installation via the plug & play system:

The plug-in module is locked into the power system module busbar. It can be locked in or unlocked whilst working. The module connection direction determines which power supply will be used.

A mixture of all of the modules can be fitted in the rails.

Technical fittings:

The plug-in module has 4 sockets available for use. The module has an integrated 16 A circuit breaker. It protects all 4 sockets. The automatic circuit breaker can be reset for switching back on if it trips out.

Technical specifications:

Single-phase voltage range: 110 V - 230 V AC 50/60 Hz,  
neutral conductor is required

Max. current per module: 16 A at 230 V AC

Temperature application range: +5°C - +45°C

Humidity range: 5% - 95% relative humidity,  
non-condensing

Protection category IP 20

W x H x D [mm]: 50 x 250 x 45