

Rittal – The System.

Faster – better – everywhere.



VX 8619.460 Cable clamp rail

State: 8/7/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.460 - Cable clamp rail Right-angle section for VX, TS, VX SE, AX, PC, base/plinth system VX

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

| | |
|-------------------------------------|---|
| Model No. | VX 8619.460 |
| Product description | For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth. |
| Material | Steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| VX SE installation options | In enclosure width 1800 mm, in the base |
| VX base/plinth installation options | In base/plinth width 1800 mm, in conjunction with holder/spacer |
| To fit | Base/plinth system VX |
| Dimensions | Length: 1,754 mm |
| To fit | Enclosure type: VX SE Width: = 1,800 mm |
| Suitable for width | 1,800 mm |
| Packs of | 2 pc(s). |
| Net weight | 7.7 kg |
| Gross weight | 9.38 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |
| Product description | VX Cable clamp rail, mounting angle, for W: 1800 mm |