

Rittal – The System.

Faster – better – everywhere.



DK 7264.035

Component shelf for frame attachment

State: 9/7/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7264.035 - Component shelf for frame attachment

For frame attachment, for installation in enclosures without 482.6 mm (19") accommodation, enclosure width: 600 and 800 mm, load capacity: 50 kg / 100 kg.

Features

| | |
|----------------------|---|
| Model No. | DK 7264.035 |
| Design | unslotted |
| Product description | For frame attachment, for installation in enclosures without 482.6 mm (19") accommodation. |
| Benefits | Mounting bolts or mounting rails may be installed on a 25 mm pitch pattern in the enclosure depth. Mounting hole for handles provided. |
| Applications | For installation in enclosures without 482.6 mm (19") accommodation |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 7035 |
| Supply includes | Component shelf, slotted |
| Installation options | Static installation: Component shelf, 50 kg with fixing bolts on punched section without mounting flange Static installation: Component shelf, 100 kg with mounting rails on punched sections without mounting flange Depth variable: Component shelf, 50 kg with telescopic slides on punched sections without mounting flange |
| Load capacity | 50 kg area load |
| Assembly instruction | Additionally, two punched sections with mounting flanges are required for the inner mounting level |
| Note | Max. depth of component shelves = Enclosure depth - 100 mm. |
| Dimensions | Width: 471 mm Height: 29 mm Depth: 400 mm |

Features

| | |
|-----------------------|---|
| To fit | Enclosure type: VX VX IT TS IT Width: 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 2.679 |
| Gross weight | 2.879 |
| Customs tariff number | 94039910 |
| EAN | 4028177165878 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Tender text

Component shelves for 600 mm wide network enclosures

Component shelves, W x D: 471 x 400 mm; made from 1.5 mm sheet steel, for 600 mm wide network enclosures. The component shelf can hold a maximum load of 50 kg. The height of the fitted component shelves can be adjusted using the 25 mm pitch pattern in network enclosures with a DIN pitch pattern but is infinitely adjustable in network enclosures with aluminium frames.

Material: sheet steel

Surface finish: RAL 7035

W x D dimensions: 471 x 400 mm