

Rittal – The System.

Faster – better – everywhere.



DK 7816.380

Sheet steel door, vertically divided,
solid

State: 15/3/2026 (Source: [https://www.rittal.com/en](#))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7816.380 - Sheet steel door, vertically divided, solid for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

Features

Model No.	DK 7816.380
Product description	With 130° hinges and locking rod, including comfort handle for profile half-cylinders with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.
Material	Sheet steel
Supply includes	Assembly parts
Note on Model No.	Without tubular door frame. Tubular door frame available on request.
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: DK-TS Width: 800 mm Height: 2,000 mm
Packs of	1 pc(s).
Net weight	32.68 kg
Gross weight	34.4 kg
Customs tariff number	94039910
ECLASS 8.0	27182204

Tender text

Sheet steel door, vertically divided for TS
W x H = 800 x 2000 mm

Sheet steel door with 130° hinges and assembly parts,
locking rod including comfort handle for semi-cylinder
with 3524 E security lock.
Non-vented sheet steel door.

Material: Sheet steel, spray finished in RAL 7035
For 800 mm x 2000 mm enclosures