

Rittal – The System.

Faster – better – everywhere.



DK 7979.616 PDU local metered

State: 8/12/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7979.616 - PDU local metered

High-end power distribution with local measurement of consumption data. Ideally suited for use in modern server racks and colocation data centres.

Features

Model No.	DK 7979.616
Design	Red
Benefits	Integral measurement of current (A); active power (kW); voltage (V); frequency (Hz); power (kWh) and phase angle (°) Measurement accuracy of $\pm 2\%$
Technical specifications	Error-tolerant PDU power supply redundant across all phases Connection cable, with connector, 3 m, H05VV-F3G4 mm ² Voltage V, current A, frequency Hz LCD display
Function principle	Power measurement per phase or infeed
Material	Aluminium, spray-finished, red, similar to RAL 3020 Cover: Plastic PA 6 GF30, black, similar to RAL 9005
Supply includes	PDU with local measurement, 32 A, 1-phase, red 2 angle brackets
Measurement functions, description	Measurement per phase or infeed
Dimensions	Width: 44 mm Depth: 47 mm Length: 1,308 mm
No. of sockets and type	24 x C13 / 6 x C19 IEC/EN/60320/C13 IEC/EN/60320/C19
Sockets	24 x C 13 6 x C 19 2-pole with protective contact, black
Rated operating voltage	230 V, 50 Hz/60 Hz
Rated current (max.)	32 A

Features

Power consumption	7.4 kW
Infeeds	Qty.: 1 Phases per infeed: 1~
Length of connection cable	3 m
Type of electrical connection	CEE
Directives	EMC directive 2014/30/EU Low Voltage Directive 2014/35/EU
Operating temperature range	5 °C...45 °C
Ambient humidity (non-condensing)	5...95 %
Storage temperature range	-5 °C...60 °C
To fit	Enclosure type: VX IT enclosure frame: ≥ 1,800 mm Enclosure type: TX Colocation Rack: ≥ 1,800 mm
Packs of	1 pc(s).
Net weight	3.3
Gross weight	3.5
Customs tariff number	85366990
EAN	4028177976252
ETIM 9	EC002762
ETIM 8	EC002762
ECLASS 8.0	27142606

Tender text

Rittal PDU local metered Model No.: DK 7979.616

PDU local metered 32A/1P CEE 24xC13 / 6xC19

Compact power distributor for deployment in IT server and network enclosures.

Robust aluminum housing with permanently mounted output slots, IEC 60320/C13 or IEC 60320/C19.

A fixed-mounted connection cable with CEE connector makes the PDU available for immediate deployment.

The PDU metered has extensive measurement functions for the current and power monitoring.

The integral TFT colour display enables quick access to the electrical consumption data.

The warranty for proper operation is 24 months.

Technical specifications PDU local metered:

Input voltage range (L1/N/PE): 230 VAC, 50-60Hz
input current: 32A

No. of phases: 1

Number of slots type IEC 60320/C13 (total): 24

Number of slots type IEC 60320/C13
(per fuse): 12

Number of slots type IEC 60320/C19 (total): 6

Number of slots type IEC 60320/C19
(per fuse): 3

No. of circuit breakers: 2

Hydraulic-magnetic protective circuit-breaker: 16 A

Connector PDU input:

EN 60309 / CEE

Length of connection cable: 3m

Connection cable type: H05VV-F

No. of wires: 3

Cable cross-section: 4 mm²

PDU housing width: 44mm

PDU housing depth: 47mm

PDU housing height: 1308mm

PDU material: Aluminum, painted red RAL 3020

PDU mounting adaptor included

Measurement per fuse:

Values recorded (per fuse):

Voltage (V), current (A), frequency (Hz), Power factor,
active energy (kWh), Active power(kW)
Voltage measuring range: 90V - 255V
Voltage resolution 0.1V
Current measuring range 0 - 16A/32A
Current resolution 0.1A
Measuring accuracy typ. $\pm 2\%$
Conformity: CE
Protection category: IP 20
Storage temperature: -20 °C to +60 °C
Ambient temperature: +5°C to +45°C
Ambient humidity <80% rel. humidity, non-condensing
Type: Rittal PDU local metered, Model No.: DK 7979.616