


# Rittal – The System.

Faster – better – everywhere.



## DK 7998.106

## RiMatrix S

State: 20/12/2025 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7998.106 - RiMatrix S Standard room

The standardised data centre is assembled at your premises within the context of hot aisle / cold aisle containment.



## Features

|                                         |                                                                                                                                                                                                                                             |
|-----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                               | DK 7998.106                                                                                                                                                                                                                                 |
| Product description                     | The standardised data centre is assembled at your premises within the context of hot aisle / cold aisle containment.                                                                                                                        |
| Benefits                                | Enhanced energy efficiency<br>Aisle containment is a combination of door and roof components which allow consistent separation of the hot and cold air                                                                                      |
| Supply includes                         | Advice and ROI calculation<br>Delivery and integration into the customer infrastructure<br>Commissioning and handover<br>Documentation, training and instruction<br>Hotline and service/service agreements<br>Precise-fit aisle containment |
| Clearance depth                         | 7,000 mm                                                                                                                                                                                                                                    |
| Clearance height                        | 2,722 mm                                                                                                                                                                                                                                    |
| Clearance width                         | 2,750 mm                                                                                                                                                                                                                                    |
| Climate control (ZUCS)                  | 60 kW + 10 kW<br>n+1 redundant                                                                                                                                                                                                              |
| Number of low-voltage main distributors | 1                                                                                                                                                                                                                                           |
| No. of PDU Basic                        | 14                                                                                                                                                                                                                                          |

# Features

|                                                        |                                                        |
|--------------------------------------------------------|--------------------------------------------------------|
| Serverracks (600x2000x1200mm)                          | 6                                                      |
| Combined network/server rack<br>(800 x 2000 x 1200 mm) | 1                                                      |
| Design burglar protection                              | Yes                                                    |
| Humidification and<br>dehumidification system          | optional                                               |
| Room extinguisher system                               | optional                                               |
| Design UPS                                             | 60 kW + 20 kW<br>n+1 redundant                         |
| Version                                                | Single 6                                               |
| Dimensions                                             | Width: 2,807 mm<br>Height: 2,750 mm<br>Depth: 7,067 mm |
| Packs of                                               | 1 pc(s).                                               |
| Customs tariff number                                  | 85480090                                               |
| EAN                                                    | 4028177702462                                          |
| ETIM 9                                                 | EC002499                                               |
| ECLASS 8.0                                             | 27180207                                               |

# Tender text

Standard data centre 60 kW, 6+1 racks,  
including cooling and UPS, for installation in a  
standard room,,

\*\*\*\*\*

Fully functional data centre comprising an ITC  
climate zone for the server and network systems, and a  
separate technical climate zone for the UPS equipment  
and low-voltage switchgear.

The ITC climate zone comprises a rack suite (depth  
1200 mm) with 6 server racks and a network rack, and  
is fully isolated from the climate zone for the  
electrical equipment by way of self-closing doors in  
the cold and hot aisles.

Both climate zones are enclosed by a complete housing  
of double-panelled, foamed wall and roof elements with  
a total thickness of 30 mm. The 600 mm wide hot aisle  
and the 950 mm wide cold aisle are partitioned within  
the room and are to this end provided  
with a partitioning panel which passes over the  
server/network racks.

The standard data centre incorporates a fully  
functional raised-floor construction, with air intake  
and outlet grilles in the form of dip-galvanised  
gratings.

Air-circulating cooling units (CRAC systems) are  
installed in the cavity space of the raised floor. The  
CRAC systems do not occupy space within the rack (Zero  
U-Space Cooling Systems).

A CRAC system is installed under each server rack.  
Each CRAC system offers a nominal cooling output of 12  
kW; the average heat load capacity per rack is thus 10  
kW, taking into account n+1 redundancy over the total  
number of CRAC systems.

The intake temperature for cooling is 20°C, observing temperature limit values according to ASHRAE 2008 (max. 27°C) within the cold aisle.

The UPS climate zone possesses a further CRAC system to dissipate the UPS heat loss. Through direct injection of the UPS cooling air, a temperature level of max. 22°C is maintained within the climate zone, in accordance with the Eurobat guidelines on the environment for 10-year batteries.

The cooled intake air is blown into the cold aisle by EC fans under the floor gratings. Flat filter fleeces are fitted between the fan grilles and the floor gratings to filter the circulating air.

The intake temperature and speed of the EC fans are regulated by a controller in the standard data centre, which communicates with the controller of an optional chiller station via a system bus for purposes of energy efficiency optimisation. The controller is not accommodated in the IT racks and thus does not occupy rack installation space.

The standard data centre is equipped ready for use with a cold piping system comprising polypropylene piping; the individual heat exchangers are connected by way of high-pressure hoses.

Required chiller set provided by the customer:

The standard data centre must be equipped with a straight ball valve to regulate the air intake temperature to the target value, a flowmeter and two temperature sensors to measure the coolant flow volume and the feed and return temperatures, as well as to calculate the heat output.

Required chiller set must be supplied:

The standard data centre must be supplied without ball valve and sensors for the coolant.

The volume of the medium is regulated by the variable-speed pump of the chiller station of the

standard data centre; the sensors are fitted in the chiller station.

The standard data centre is equipped with a modular UPS system with 20 kW modules. The system provides for n+1 redundancy, and thus four UPS modules are supplied to cover the possible connected load of 60 kW for the ITC hardware.

The UPS system possesses 10 battery strings with 28 Ah batteries, which are assigned jointly to all UPS modules and ensure autonomy for a period of 13 minutes.

The standard data centre incorporates switchgear with fused feeders for the installed rack suite. The switchgear spreads the feeders over two panels to establish an A/B power supply. The UPS system feeds supply path A. Supply path B must be connected to the mains supply via overvoltage protection.

From the switchgear, the distribution busbars of the individual racks are wired ready for use and comprise Power Distribution Units with 24 C13 and 6 C19 sockets. Each rack is provided with two PDUs to establish an A/B power supply.

The power supply is routed above the racks. The data cables are routed to the IT racks separately from the power supply cables. The installation of the data cables is to be performed by the site operator/customer.

Lighting and service socket are protected by way of an RCCB. Emergency lighting is installed.

The standard data centre is equipped with an early fire detection system. To this end, air is drawn from the raised floor of the hot aisle via a perforated plastic pipe. The alarm is given by a monitoring system with Web access and SNMP interface.

The standard data centre is assembled and installed directly on the customer's premises (without IT cabling; connection to the chiller and mains power supply are to be ordered separately).

Standard data centre version with 6+1 racks for a standard room

”

Outside dimensions,,Inside dimensions,,  
Length:,,7060 mm,,Length:,,7000 mm,,  
Width:,,2810 mm,,Width:,,2750 mm,,  
Height:,,2740 mm,,Height:,,2710 mm,,

””

Walls without door require an assembly clearance of 100 mm to the building walls. The roof of the enclosures requires an assembly clearance of 200 mm to the building ceiling.,,