

Rittal – The System.

Faster – better – everywhere.



VX 8619.450

Cable clamp rail

State: 30/1/2026 (Source: rittal.com/in-en)



FRIEDHELM LOH GROUP

VX 8619.450 - Cable clamp rail Right-angle section for VX, TS, VX SE, PC, base/plinth system VX

For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.

Features

Model No.	VX 8619.450
Product description	For strain relief with cable entry. Depth-variable mounting on a 25 mm pitch pattern on the horizontal enclosure section or in the base/plinth.
Material	Steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX SE installation options	In enclosure width 1600 mm, in the base
VX base/plinth installation options	In base/plinth width 1600 mm, in conjunction with holder/spacer
To fit	Base/plinth system VX
Dimensions	Length: 1,554 mm
To fit	Enclosure type: VX SE CX pedestal Width: = 1,600 mm
Suitable for width	1,600 mm
Packs of	2 pc(s).
Net weight	7.9
Gross weight	8.28
Customs tariff number	73269098
EAN	4028177921979
ETIM 9	EC000322
ECLASS 8.0	27400604