

Rittal – The System.

Faster – better – everywhere.



SV 9677.900 Connection adaptor

State: 2/8/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.900 - Connection adaptor

For the connection of round conductors. For bar systems with 185 mm centre-to-centre spacing.

Features

Model No.	SV 9677.900
Material	Chassis: Fibreglass-reinforced polyester Fire protection corresponding to UL 94-V0
Colour	RAL 7035
For bar systems with centre-to-centre spacing	185 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M12
Number of poles	3-pole
Rated current max.	800 A
Rated operating voltage	690 V, 3~
Note	When using components on busbars with contact hazard protection cover, the contact terminal must be used
Dimensions	Width: 100 mm Height: 665 mm
Connection of round conductors	6 - 240 mm ²
To fit busbars	Height: 10 mm
Packs of	1 pc(s).
Net weight	4.5
Gross weight	5
Copper weight (kg per piece)	3.128
Customs tariff number	85369010
EAN	4028177705289
ETIM 9	EC001531

Features

ECLASS 8.0	27370304
------------	----------

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---