


Rittal – The System.

Faster – better – everywhere.



undefined 9792.117 Ex enclosures

State: 12/9/2025 (Source: rittal.com/in-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

undefined 9792.117 - Ex enclosures Stainless steel, empty enclosure with hinged door

Features

Model No.	9792.117
Benefits	Zone 1 and 2 or 21 and 22 to 2014/34/EC Protection type to EN 60 079: Equipment protection due to increased safety, equipment protection due to enclosure
Material	Enclosure frame: Stainless steel 1.4301 (AISI 304) Door: Stainless steel, all-round foamed-in PU seal Roof: Stainless steel 1.4301 (AISI 304) Rear panel: Stainless steel 1.4301 (AISI 304) Side panels: Stainless steel 1.4301 (AISI 304) Mounting plate: Sheet steel, zinc-plated
Surface finish	Enclosure: Outside 4B, Inside 2B Mounting plate: Sheet steel, zinc-plated
Supply includes	Enclosure frame Door(s) Reinforcement section in the door Roof plate Rear panel Side panels left and right Mounting plate 4 eyebolts Lock: 3 mm double-bit 2 punched rails 18 x 39 mm
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
Dimensions mounting plate (W x H)	699 mm x 1,896 mm
Material thickness - enclosure	2 mm

Features

Material thickness of mounting plate	3 mm
Material thickness - door	2 mm
IP protection category to IEC 60529	IP 66
Operating temperature range	-50 °C...180 °C
Operating temperature	The specified temperatures may be limited by the installed equipment
Packs of	1 pc(s).
EAN	4028177979611

Approvals

Approvals	ATEX IEC Ex
-----------	----------------