


Rittal – The System.

Faster – better – everywhere.



AX 1350.450

Armadi compatti AX

Stato: 22/05/2025 (Fonte: rittal.com/it-it)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 1350.450 - Armadi compatti AX C4-H

The compact enclosure AX with integral enclosure locators in the roof, base and side forms the familiar 25 mm system pitch pattern from the VX25 large enclosure. System components and accessories are easily, quickly and securely installed and retrofitted on rails, with no drilling required. Surface coating to DIN EN ISO 12944 corrosion protection class C4-H. Important: Please observe the product properties and the notes on installation and maintenance in the product description.

Caratteristiche

Nr. d'ord.	AX 1350.450
Esecuzione	Surface coating to DIN EN ISO 12944
Vantaggi	Maggiori opzioni di allestimento interno grazie alla soluzione tecnica con bugnature integrate e compatibili con accessori con passo meccanico da 25 mm, in combinazione con la guida di allestimento interno e l'ampia gamma di accessori a catalogo Mantenimento del grado di protezione (approvazione UL) grazie al montaggio della chassis di allestimento interno senza forature Livello di montaggio supplementare e maggiore capacità di carico con la guida di allestimento del fondo Progettazione e configurazione semplificate con il Configuratore Rittal RiPanel
Materiale	Contentitore e porta: lamiera d'acciaio Porta: lamiera d'acciaio, guarnizione perimetrale in poliuretano iniettato
Superficie	Enclosure and door: Powder-coated, textured paint Piastra di montaggio: zincata
Colore	RAL 7035
Parti incluse nella fornitura	Contentitore con porta/e Flangia/flange sul fondo del contentitore Piastra di montaggio Listello forato della porta Chiusura: doppio pettine 3 mm

Caratteristiche

Nota	Installation and maintenance: DIN EN ISO 12944 refers to corrosion protection for steel structures (e.g. containers and bridges) and is thus only indirectly applicable to enclosures. The test criteria defined in this standard were nevertheless applied to the paint finishes of the C4-H enclosures. Our "paint finish equivalent to C4-H" thus satisfies all requirements of the standard in respect of the 720-hour salt spray mist test. Even so, corrosion can still occur on such sheet-steel enclosures. If the enclosure is installed in an environment where there is a risk of corrosion, the user must provide for regular maintenance and the prompt repairing of any paint damage. Depending on the application, the user may need to take suitable precautions as protection against environmental conditions at the place of installation, e.g. UV radiation.
Grado di protezione NEMA	NEMA 1, 3R, 4, 12
Grado di protezione IP secondo EN 60 529	IP 66
Codice IK	IK10
Dimensioni	Larghezza: 500 mm Altezza: 500 mm Profondità: 300 mm
Spessore piastra di montaggio	2,5 mm
Dimensioni piastra di montaggio (L x A)	450 mm x 475 mm
Numero di porte	1
Battuta della porta reversibile	sì
Chiusura	Esecuzione della chiusura: Chiusura a filo Numero di chiusure: 2 Inserto di chiusura: Doppio pettine 3 mm
Flangia	Grandezza: 6 Quantità: 1
Materiale di base	Lamiera d'acciaio
Confezione	1 pz.
PCF per pack (cradle-to-gate)	74,4 kg CO2 eq (Cat B)

Caratteristiche

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177993785
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101