

Rittal – The System.

Faster – better – everywhere.



RX 9360.512

State: 2025/06/27 (Source: [rittal.com/jp-ja](https://www.rittal.com/jp-ja))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.512 -

CB component adaptor (3-pole, max. 250 A) for the RiLineX busbar platform and 60 mm busbar systems such as RiLine60. The device width on the busbar system is 105 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free, snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

品番	RX 9360.512
仕様	Easy Fix
メリット	コンパクト サーキットブレーカー (MCCB) をボード上に直接設置 Tool-free changeover of the cable outlet Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure High rated voltage 800 V ready
材質	ポリアミド (PA 6) 耐燃性 UL 94 適合
塗装色	RAL 9005 RAL 35745

Features

同梱品	3 connection space covers
保護等級 IP (IEC 60 529 準拠)	IP 2XB
定格電流 最大	250 A
定格インパルス電圧 Uimp	12 kV
定格電圧	1,000 V AC 1,500 V DC 600 V AC (UL) 1,500 V DC (UL)
Rated insulation voltage	1,500 kV
Rated impulse withstand current	80 mA
過電圧カテゴリー	4
汚染度	3
極数	3 極
ケーブル引き出し口	下
電源接続	ねじ M8

Features

適用メーカー (タイプ)	ABB (S3 150, S3 225, S3, T3, T4, XT3, XT4, FE160, FE250) Chint (NM8N-250, NM1-250H, NXM-250S, NXMS-250) Eaton (LZMB2-A160, LZMB2-A250) Fuji Electric (BW160_-3P, BW250_-3) Hager (P250) Himel (HDM3-160, HDM3-250, HDM3L-160, HDM3L-250) Hyundai Electric (160, 250AF) Legrand (DPX250, DPX ³ 250) LS Electric (250AF, TS250) Mitsubishi (NF125-SGV, NF160-SGV, NF250-SV) OEZ (BD250) Rockwell (140G-J0F3-D25) Sassin (3SM8N-225, 3SM8L-225) Schneider (EZC250H, NS100, NS160, NS250, NSX100, NSX160, NSX250, GV5) Schrack (MC2) Siemens (3VA20, 3VA21, 3VA22, 3VT2, 3RV1063, 3RV1363, 3RV1364, VL160/3VL2) Terasaki (S160, S250, H250)
適用バスバーシステム	RiLineX RiLine60
基本周波数	50...60 Hz
湿度(結露無きこと)	10...90 %
適用バスバー	15 x 5/10 20 x 5/10 30 x 5/10
動作温度範囲	-25 °C...55 °C
保管温度範囲	-25 °C...75 °C

Features

寸法：	幅: 105 mm 高さ: 252 mm 奥行: 63 mm
1パック	1 個
純質量	1.46
総質量	1.608
銅の含有量 (kg / 個)	0.608
関税率番号	85369095
EAN	4028177997134
ETIM 9	EC001531

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------