## Rittal – The System.

Faster - better - everywhere.





# SV 9345.610 CB 장치 <u>어댑터</u>

상태: 2025. 12. 18 (원천: rittal.com/kr-ko)



### SV 9345.610 - CB 장치 어댑터 3극

회로 차단기의 간단한 범용 조립을 위한 회로 차단기 장치 어댑터.



#### 특징

주문 번호	SV 9345.610
재료	폴리아미드 UL 94-V0 에 준하는 화재 방지 등급
색상	RAL 7035
제공 범위	연결 스트립 슬롯 너트
정격 전류최대	250 A
정격 작동 전압	690V, 3~
전기 사양 UL(SCCR)	65kA - 480V, 회로 차단기 최대 250A, DIVQ/7
케이블 출력부	하부
중심 간격이 있는 바 시스템용	60 mm
참고 사항	케이블 출력부: 스위치 출력 또는 스위치기어의 출력 케이블프 제시된 기술 자료가 UL 애플리케이션에 맞지 않을 수 있음.
	3극
치수	폭: 105 mm 높이: 240 mm

© Rittal 2025

## 특징

높이: 5, 10 mm  ABB (S3, T3, T4/320 A, T3 UL, T4 UL, XT3, XT4)  Allen Bradley (140U-J)  Eaton (NZM2, NZM2 UL, BZM B2)  GE (FE160, FE250, FD160)  Legrand (DPX 250)  Mitsubishi (NF125-SGW/HGW, NF160-SGW/HGW)  OEZ (BD250N, BD250S)  Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)  Schrack (MC2)
Allen Bradley (140U-J) Eaton (NZM2, NZM2 UL, BZM B2) GE (FE160, FE250, FD160) Legrand (DPX 250) Mitsubishi (NF125-SGW/HGW, NF160-SGW/HGW) OEZ (BD250N, BD250S) Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)
Eaton (NZM2, NZM2 UL, BZM B2) GE (FE160, FE250, FD160) Legrand (DPX 250) Mitsubishi (NF125-SGW/HGW, NF160-SGW/HGW) OEZ (BD250N, BD250S) Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)
GE (FE160, FE250, FD160) Legrand (DPX 250) Mitsubishi (NF125-SGW/HGW, NF160-SGW/HGW) OEZ (BD250N, BD250S) Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)
Legrand (DPX 250) Mitsubishi (NF125-SGW/HGW, NF160-SGW/HGW) OEZ (BD250N, BD250S) Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)
Mitsubishi (NF125-SGW/HGW, NF160-SGW/HGW) OEZ (BD250N, BD250S) Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)
OEZ (BD250N, BD250S) Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)
Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)
NSF250)
·
Schrack (MC2)
Siemens (VL150(X) UL, VL160(X), VL250, VL250 UL, 3RV10 63,
3RV13 63, 3RV13 64, 3VT2, 3VA12/20/21/22, 3VA52/61/62)
Terasaki (H125, L125, H160, L160, S160, E250, H250, L250)
UL
1 개
1.433
1.515
0.77
85369095
4028177679986
EC001531
27370304

## 승인

© Rittal 2025 3

#### 승인

승인	ABS
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
설명	적합성 인증
	적합성 인증 UK

© Rittal 2025 4