Rittal – The System.

Faster - better - everywhere.





IT 7100.120 OCP ORV3 rack


Состояние: 17.11.2025 (Источник: rittal.com/kz-ru)



IT 7100.120 - OCP ORV3 rack

OCP is an ambitious international community that aims to simplify and optimise IT infrastructure. The Rittal OCP ORV3 rack is OCP accepted and ready for immediate use. Simple modifications and enhancements can be made as and when required, thanks to the range of accessories. The OCP ORV3 rack can also accommodate a Direct Liquid Cooling (DLC) solution. Take your efficiency and performance density to a whole new level with this rack.







Функции

Арт. №	IT 7100.120
Исполнение	Open frame
	with busbar
	Prepared for cable entry in roof and base
	Cable routing at the front, across the full height
Преимущества	Prepared to accommodate 21" OCP components and direct contact on the busbar
	Rapid construction and service thanks to click-in fitting of the IT and IT OCP Power rail system
	End-to-end cable management in front rack over full height
	Ideal for high-performance computing and AI technology thanks to
	being ready for Direct Liquid Cooling solutions that are designed to
	dissipate the thermal load generated in the rack
	Integrated heavy-duty castors make transportation easier and
	ensure ease of handling in the data centre
Технические характеристики	Rated operating voltage: 48 V DC / power consumption 18 kW
Материал	Листовая сталь
Поверхность	Грунтовка, снаружи порошковое покрытие
Цвет	RAL 9005

© Rittal 2025 2

Функции

Комплект поставки	OCP ORV3 rack
	OCP busbar for max. 48 DC/18 kW
	2 bracing struts, pre-assembled
	Levelling feet, pre-assembled
	4 castors (freely rotating)
	Уплотнение для соединения в линейку
	Воздуховодная панель
Размер	Ширина: 600 мм
	Высота: 2.286 мм
	Глубина: 1.068 мм
Единиц высоты	44 OU
Нагрузочная способность	14 000 N
Основной материал	Листовая сталь
Упаковка	1 шт.
Вес нетто	172
Gross weight	200
Код ТНВЭД	94032080
EAN	4028177997738
ETIM 9	EC002499
ETIM 8	EC002499
ECLASS 8.0	27180207

Одобрения

Одобрения	IEC CB UL + C-UL (listed)
Объяснения	Декларация о соответствии

© Rittal 2025 3