

**Rittal – The System.**

Faster – better – everywhere.



**SV 9343.330**

**NH fuse-switch disconnecter**

State: 2/2/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9343.330 - NH fuse-switch disconnecter with electronic fuse monitoring

## Features

|   |   |
|---|---|
| Model No.                                     | SV 9343.330   |
| Design  | For 60 mm busbar systems with electronic fuse monitoring  |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated |
| Colour  | Chassis: RAL 7035<br>Cover: RAL 7035/7001   |
| Clamping area for laminated copper bars       | Clamping area width: 50 mm<br>Clamping area height: 10 mm   |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Cable outlet                                  | Top/bottom  |
| Type of electrical connection                 | Screw M10   |
| Rated operating current max.                  | 630 A   |
| Rated operating voltage                       | 400 V - 690 V, 3~   |
| For NH size                                   | 3   |
| Test specification                            | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts)   |
| Dimensions                                    | Width: 250 mm<br>Height: 298 mm   |
| Connection of round conductors                | 10 - 300 mm <sup>2</sup>  |
| To fit busbars                                | Height: 5, 10 mm  |
| Number of poles                               | 3-pole  |
| with electronic fuse monitoring               | Yes   |

# Features

---

|                               |                          |
|-------------------------------|--------------------------|
| Round conductor cross-section | 10 - 300 mm <sup>2</sup> |
| Packs of                      | 1 pc(s).                 |
| Net weight                    | 4.28                     |
| Gross weight                  | 4.38                     |
| Copper weight (kg per piece)  | 1.44                     |
| Customs tariff number         | 85369095                 |
| EAN                           | 4028177540477            |
| ETIM 9                        | EC000249                 |
| ECLASS 8.0                    | 27371401                 |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | CQC-CCC   |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |