


# Rittal – The System.

Faster – better – everywhere.



## IT 7100.120 OCP ORV3 rack

Состояние: 08.07.2026 (Источник: [rittal.com/kz-ru](http://rittal.com/kz-ru))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 7100.120 - OCP ORV3 rack

OCP is an ambitious international community that aims to simplify and optimise IT infrastructure. The Rittal OCP ORV3 rack is OCP accepted and ready for immediate use. Simple modifications and enhancements can be made as and when required, thanks to the range of accessories. The OCP ORV3 rack can also accommodate a Direct Liquid Cooling (DLC) solution. Take your efficiency and performance density to a whole new level with this rack.



## Функции

Арт. №	IT 7100.120
Исполнение	Open frame with busbar Prepared for cable entry in roof and base Cable routing at the front, across the full height
Преимущества	Prepared to accommodate 21" OCP components and direct contact on the busbar Rapid construction and service thanks to click-in fitting of the IT and IT OCP Power rail system End-to-end cable management in front rack over full height Ideal for high-performance computing and AI technology thanks to being ready for Direct Liquid Cooling solutions that are designed to dissipate the thermal load generated in the rack Integrated heavy-duty castors make transportation easier and ensure ease of handling in the data centre
Материал	Листовая сталь
Поверхность	Грунтовка, снаружи порошковое покрытие
Цвет	RAL 9005

## Функции

Комплект поставки	ОСР ORV3 rack ОСР busbar for max. 48 DC/18 kW 2 bracing struts, pre-assembled Levelling feet, pre-assembled 4 castors (freely rotating) Уплотнение для соединения в линейку Воздуховодная панель
Размер	Ширина: 600 мм Высота: 2.286 мм Глубина: 1.068 мм
Единиц высоты	44 OU
Нагрузочная способность	14 000 N
Основной материал	Листовая сталь
Номинальная мощность	18 кВт
Номинальное рабочее напряжение	48 В DC
Упаковка	1 шт.
Вес нетто	172 kg
Gross weight	200 kg
Код ТНВЭД	94032080
ETIM 9	EC002499
ETIM 8	EC002499
ECLASS 8.0	27180207
Описание продукта	ОСР ORV3 rack, with busbar, 44 OU, WxHxD: 600 x 2286 x 1068 mm, RAL 9005

## Одобрения

Одобрения	IEC CB UL + C-UL (listed)
-----------	------------------------------

# Одобрения

---

Обяснения

Декларация о соответствии