

Rittal – The System.

Faster – better – everywhere.



RX 9360.241

RiLineX connection adaptor

Состояние: 10.06.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.241 - RiLineX connection adaptor

RiLineX connection adaptor for side infeed from the left or right. For use with vertical mounting of the board or as a corner connector using laminated connection straps. It is also ideal as a T-connection between horizontal and vertical systems. It must not be used with other busbar systems such as RiLine60.



Функции

Арт. №	RX 9360.241
Преимущества	Mounting on the busbar system and cable connection with just one screw Vertical variant for side infeed to the board
Материал	Полиамид (PA 6) Негорючесть согласно UL 94
Цвет	RAL 35745
Rated current (reference value, IEC)	432 A
Rated current of round conductor max.(IEC)	710 A
Rated current of round conductor max. (UL)	630 A
Rated current of laminated copper bar max. (IEC)	950 A

Функции

Rated current of laminated copper bar max. (UL)	910 A
Указание	<p>The specified rated current, given as a reference value, is based on the recommended maximum operating current for single-core cable with a permissible conductor temperature of 70 °C in accordance with IEC 61439-1, Table H.1, installation spaced horizontally in free air at an ambient temperature of 55 °C.</p> <p>The specified rated current max. (IEC) describes the recommended maximum operating current of the terminal connection with a temperature rise limit of 70 K in accordance with IEC 61439-1 (Table 6) for conductors spaced free in air. The permissible insulation temperature must be observed.</p>
Electrical ratings UL (SCCR)	27,5 kA - 600 V, RMS, unprotected 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 100 kA - 600 V, Fuse Class L max. 1200 A, JDDZ/7
Отвод проводов	In an axial direction to the board
Для шинных систем с межцентровым расстоянием	60 mm
Количество полюсов	3-пол.
Подходит для шинной системы	RiLineX RiLine60
Размер	Ширина: 57,8 мм Высота: 239,4 мм Глубина: 135,6 мм
Подключение проводов	150 - 300 мм ²
Клемма для гибких медных шин (Ш x В)	32 x 20 мм
Подходит для шин	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	1 000 V AC 1 500 V DC 600 V AC (UL) 600 V DC (UL)
Степень загрязнения	3

Функции

Стандарты	IEC/EN 61439-1 UL 508
Номинальное импульсное напряжение U_{imp}	12 кВ
Номинальное напряжение изоляции U_i	1 000 В
Тепловыделение макс.	50 Вт
Степень защиты IP согл. МЭК 60 529	IP 2X
Maximum operating air humidity	90 %
Диапазон рабочих температур	-5 °C...55 °C
Диапазон температур хранения	-25 °C...75 °C
Влажность воздуха (без конденсата)	10...90 %
Упаковка	1 шт.
Вес нетто	1 kg
Gross weight	1,185 kg
PCF per pack (cradle-to-gate)	5,51
Код ТНВЭД	85369010
ETIM 9	EC001531
Описание продукта	RiLineX connection adaptor for side infeed from the left or right. For use with vertical mounting of the board or as a corner connector using laminated connection straps. It is also ideal as a T-connection between horizontal and vertical systems. It must not be used with other busbar systems such as RiLine60.

Одобрения

Одобрения	UL + C-UL (listed)
-----------	--------------------

Одобрения

Обяснения

Декларация о соответствии
PCF-declaration