


Rittal – The System.

Faster – better – everywhere.



RX 9361.315

RiLineX connection adaptor

Состояние: 30.05.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.315 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The connection adaptor is single-pole and fits a double connection (round/sector-shaped conductor). The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adaptor boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adaptor is readily installed on RiLine60. It offers high levels of short-circuit protection and easy-to-fit contact hazard protection.



Функции

Арт. №	RX 9361.315
Преимущества	Mounting on the busbar system and cable connection with just one screw
Материал	Полиамид (PA 6) Негорючесть согласно UL 94
Цвет	RAL 9005
Номинальный ток (макс.)	864 A
Номинальный ток макс.	1 060 A
Rated current of round conductor	1 060 A
Rated current of round conductor (UL)	980 A

Функции

Electrical ratings UL (SCCR)	27,5 kA - 600 V, RMS, unprotected 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 600 V, Fuse Class L max. 2000 A, JDDZ/7
Отвод проводов	сверху/снизу
Для шинных систем с межцентровым расстоянием	60 mm
Количество полюсов	1-пол.
Подходит для шинной системы	RiLineX RiLine60
Размер	Ширина: 54,1 мм Высота: 119,4 мм Глубина: 163,4 мм
Подключение проводов	95 - 300 мм ²
Подходит для шин	15 x 10 20 x 10 30 x 10
Rated voltage	1 000 V AC 1 500 V DC 600 V AC (UL) 600 V DC (UL)
Категория перенапряжения	4
Степень загрязнения	3
Стандарты	IEC/EN 61439-1 UL 508
Номинальное импульсное напряжение U _{imp}	12 кВ
Номинальное напряжение изоляции U _i	1 000 В
Тепловыделение макс.	105 Вт
Степень защиты IP согл. МЭК 60529	IP 2X
Maximum operating air humidity	90 %

Функции

Диапазон рабочих температур	-5 °C...55 °C
Диапазон температур хранения	-25 °C...75 °C
Влажность воздуха (без конденсата)	10...90 %
Кол-во подключений	2
Упаковка	1 шт.
Вес нетто	0,8 kg
Gross weight	0,892 kg
PCF per pack (cradle-to-gate)	4,47
Код ТНВЭД	85369010
ETIM 9	EC001531

Описание продукта	<p>RiLineX connection adaptor for 60 mm busbar systems. The connection adaptor is single-pole and fits a double connection (round/sector-shaped conductor). The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adaptor boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adaptor is readily installed on RiLine60. It offers high levels of short-circuit protection and easy-to-fit contact hazard protection.</p>
-------------------	--

Одобрения

Одобрения	UL + C-UL (listed)
Объяснения	Декларация о соответствии PCF-declaration