

# Rittal – The System.

Faster – better – everywhere.



## SV 9393.561 Current transformer

State: 11/5/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9393.561 - Current transformer

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SV 9393.561   |
| Design                            | Output voltage 333 mV   |
| Material                          | Polyamide<br>Fire protection corresponding to UL 94                                   |
| Colour                            | RAL 9005  |
| Supply includes                   | 2 plug-in feet<br>2 insulating caps<br>1 primary bar clamp<br>2 grub screws           |
| To fit busbars                    | 60 x 15<br>2 x 50 x 10  |
| Primary current                   | 800 A   |
| Standards                         | EN 61869-1/ 2<br>EN 42600<br>VDE 0100<br>EN 50274 / VDE 0660-514<br>DGUV regulation 3 |
| Dimensions                        | Width: 85 mm<br>Height: 108 mm<br>Depth: 30 mm  |
| Operating temperature range       | -5 °C...55 °C   |
| Storage temperature range         | -25 °C...75 °C  |
| Ambient humidity (non-condensing) | 10...90 %   |
| Fundamental frequency             | 50...60 Hz  |
| Accuracy Class                    | 0.5   |
| Insulation material (class)       | F   |

# Features

---

|                       |                                     |
|-----------------------|-------------------------------------|
| Packs of              | 1 pc(s).                            |
| Net weight            | 0.32 kg                             |
| Gross weight          | 0.331 kg                            |
| Customs tariff number | 85043129                            |
| ETIM 9                | EC002048                            |
| Product description   | SV Current transformer 800 A, 52 mm |

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|