

**Rittal – The System.**

Faster – better – everywhere.



**PK 9518.100**

**Polycarbonate enclosures PK**

State: 28/6/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9518.100 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

Model No.	PK 9518.100
Design	PK enclosure with transparent cover
Product description	Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover transparent: Polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

# Features

---

Dimensions	Width: 182 mm Height: 180 mm Depth: 111 mm
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	1 pc(s).
Net weight	0.627 kg
Gross weight	0.72 kg
Customs tariff number	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	PK Polycarbonate enclosure, WHD: 182x180x111 mm, fibreglass-reinforced polycarbonate, without knockouts, with transparent cover

---

# Approvals

---

Approvals	C-UL DNV UL
Explanations	Declaration of conformity

---

# Tender text

## Polycarbonate Housings without knockouts

Polycarbonate enclosure, transparent cover without knockouts

Enclosure: Fibreglass-reinforced polycarbonate  
without knockouts for cable entry

Cover: Fibreglass-reinforced polycarbonate  
all-round foamed-in PU seal

Cover screws: Polyamide

Insulating bungs: Polyethylene

Supply includes: Cover screws

Insulating bungs for wall mounting screws

Accessories: Wall mounting bracket

Protection category to IEC 60 529: IP 66

Protection category NEMA: NEMA 4X

Colour: similar to RAL 7035

Dimensions (W x H x T): 182 x 180 x 111 mm