

Rittal – The System.

Faster – better – everywhere.



PK 9522.000

Polycarbonate enclosures PK

State: 14/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9522.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



Features

Model No.	PK 9522.000
Design	PK enclosure with solid cover
Product description	Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

Features

Dimensions	Width: 254 mm Height: 180 mm Depth: 165 mm
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	1 pc(s).
Net weight	1 kg
Gross weight	1.164 kg
Customs tariff number	84879090
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	PK Polycarbonate enclosure, WHD: 254x180x165 mm, fibreglass-reinforced polycarbonate, without knockouts, with grey cover

Approvals

Approvals	C-UL DNV UL
Explanations	Declaration of conformity

Tender text

Polycarbonate Housings without knockouts

Polycarbonate enclosure with solid cover without knockouts

Enclosure: Fibreglass-reinforced polycarbonate

without knockouts for cable entry

Cover: Fibreglass-reinforced polycarbonate

all-round foamed-in PU seal

Cover screws: Polyamide

Insulating bungs: Polyethylene

Supply includes: Cover screws

Insulating bungs for wall mounting screws

Accessories: Wall mounting bracket

Protection category to IEC 60 529: IP 66

Protection category NEMA: NEMA 4X

Colour: similar to RAL 7035

Dimensions (W x H x T): 254 x 180 x 165 mm