
### Rittal - The System.

Faster – better – everywhere.





## SV 9661.240 PE/PEN combination angle E-Cu

State: 4/11/2025 (Source: rittal.com/in-en)



# SV 9661.240 - PE/PEN combination angle E-Cu for PE/PEN combinations

The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.

#### **Features**

Model No.	SV 9661.240
Product description	The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.
Benefits	Thanks to the pre-assembled combination angles, baying brackets and busbars customised to match the enclosure width, assembly is time-saving with cost reduction
Applications	Form 2-4
Material	E-Cu
Supply includes	Assembly parts
Approved short-circuit current capability	Icw 60 kA, 1 sec.
To fit busbars	Busbar E-Cu with integral punchings
OUT_CROSS_SECTION_COL_SM	40 - 10 mm
To fit busbars	Width: 40, 80 Height: 10, 10 mm
Packs of	4 pc(s).
Net weight	2.2
Gross weight	2.356
Copper weight (kg per piece)	0.45
Customs tariff number	74198090
EAN	4028177555808
ETIM 9	EC000329

© Rittal 2025 2

#### **Features**

ECLASS 8.0 27400605

## **Approvals**

Explanations Declaration of conformity

Declaration of conformity UK

© Rittal 2025 3