

Rittal – The System.

Faster – better – everywhere.



DK 9788.271

PS Networking Enclosures

State: 9/4/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 9788.271 - PS Networking Enclosures

Rittals rugged PS networking enclosures are an ideal solution for network applications. The cabinets rugged construction offers the highest stability as well as high-load bearing capacity.



Features

Model No.	DK 9788.271
Product description	Rittals rugged PS networking enclosures are an ideal solution for network applications. The cabinets rugged construction offers the highest stability as well as high-load bearing capacity.
Benefits	Frames are bayable, scalable and modular Static load capacity of 1.000 kg on 19" mounting angles (total load of 1.400 kg on enclosure frame) Comply to EIA 310 and IEC 297 standards
Material	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Base: sheet steel, 1.5 mm Mounting angles: Sheet steel, 2 mm
Surface finish	dipcoat-primed and powder-coated, textured paint Mounting angles: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame Roof plate with cable entry Base plate with cable entry 482.6 mm (19") level, L-shaped mounting angles front and rear on Vertical Cable Trough (LH & RH) on 6 x punched section
Note	Net weight

Features

Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
------------	--

Packs of	1 pc(s).
----------	----------