

Rittal – The System.

Faster – better – everywhere.



undefined 9792.124 Ex enclosures

State: 11/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



undefined 9792.124 - Ex enclosures stainless steel, empty enclosure with hinged door



Features

Model No.	9792.124
Benefits	Zone 1 and 2 or 21 and 22 to 2014/34/EC Protection type to EN 60 079: Equipment protection due to increased safety, equipment protection due to enclosure
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Sheet steel, zinc-plated
Surface finish	Enclosure: Outside 4B, Inside 2B Mounting plate: Sheet steel, zinc-plated
Supply includes	Enclosure Door Mounting plate Reinforcement section in the door
Dimensions	Width: 600 mm Height: 600 mm Depth: 210 mm
Dimensions mounting plate (W x H)	539 mm x 560 mm
Material thickness - enclosure	1.5 mm

Features

Material thickness of mounting plate	3 mm
Material thickness - door	1.5 mm
Basic material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Cam lock with 3 mm double-bit lock insert Number of locks: 2
IP protection category to IEC 60529	IP 66
Operating temperature range	-50 °C...180 °C
Operating temperature	The specified temperatures may be limited by the installed equipment
Packs of	1 pc(s).

Approvals

Approvals	ATEX IECEX UR + C-UR (recognized)
Explanations	Attestation of Conformity
