


# Rittal – The System.

Faster – better – everywhere.



## AS 4051.192

# Wire Terminal WT L fully automated wire processing machine

Состояние: 15.05.2026 (Источник: [rittal.com/kz-ru](http://rittal.com/kz-ru))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.192 - Wire Terminal WT L fully automated wire processing machine

The Wire Terminal WT L5 T fully automated wire processing machine can process wire cross-sections ranging from 0.5–2.5 mm<sup>2</sup>. This includes length-cutting, insulation-stripping, crimping and project-specific labelling of the wires. The pre-assembled wires are made available by the Wire Handling System (WHS). The WHS is a fully automated wire distribution system. Wires that have been manufactured just-in-time in the Wire Terminal WT are delivered sequentially to a maximum of four wiring workstations using compressed air.



## Функции

Арт. №	AS 4051.192
Исполнение	Wire Terminal WT L5 T (Wire Handling System)
Преимущества	Wire manufacturing based on the just-in-time and just-in-sequence principles Save time and resources with automated wire infeed Step-by-step operative instructions with Eplan Smart Production Direct addressing helps to minimise errors in workstation commissioning

# Функции

---

Технические характеристики	<p>5 wire end ferrule infeeds via feeder bowls</p> <p>Crimping range 0.5 mm<sup>2</sup>: Crimping length 8 mm (0.31 in.) and 10 mm (0.39 in.)</p> <p>Crimping range 0.75 mm<sup>2</sup>: Crimping length 8 mm (0.31 in.), 10 mm (0.39 in.) and 12 mm (0.47 in.)</p> <p>Crimping range 1 mm<sup>2</sup>: Crimping length 8 mm (0.31 in.), 10 mm (0.39 in.) and 12 mm (0.47 in.)</p> <p>Crimping range 1.5 mm<sup>2</sup>: Crimping length 8 mm (0.31 in.), 10 mm (0.39 in.), 12 mm (0.47 in.) und 18 mm (0.71 in.)</p> <p>Crimping range 2.5 mm<sup>2</sup>: Crimping length 8 mm (0.31 in.), 12 mm (0.47 in.) and 18 mm (0.71 in.)</p> <p>Wire output via the integral Wire Handling System</p> <p>The Wire Terminal WT L can process wire lengths from 150 mm to 10 m</p> <p>The WT L Wire Terminal can accommodate one wire infeed block.</p>
Комплект поставки	<p>Каркас и корпус машины</p> <p>Элемент управления</p> <p>1 x WT 16 vibratory bowl feeder for 0.5 mm<sup>2</sup></p> <p>2 x WT 20 vibratory bowl feeders for 0.75/1.0 mm<sup>2</sup></p> <p>2 x WT 29 vibratory bowl feeders for 1.5/2.5 mm<sup>2</sup></p> <p>Wire distribution system for the wire handling system</p>
Обрабатываемый материал	Wire end ferrules with plastic collar to DIN 46228-4 and Multinorm
Указание	<p>По вопросам индивидуального оборудования машины обращайтесь к Вашему консультанту Rittal.</p> <p>Стандартный комплект поставки Wire Terminals включает в себя языки немецкий и английский</p> <p>The vibratory bowl feeders and the separation of single wire end ferrules are designed for the dimensional tolerances of Rittal wire end ferrules to DIN 46228-4:2019-02. If the wire end ferrules used exceed the defined dimension tolerances, it may be necessary to design/test a new bowl feeder and to adapt the wire end ferrule separation.</p> <p>Возможны технические изменения</p>
Опции машины	<p>Wire store WT Tube 12 (4051.218)</p> <p>WT printer IQ.JET, black 4051281</p> <p>WT printer IQ.JET, white 4051280</p>
Интерфейсы	<p>Eplan Pro Panel</p> <p>Eplan Smart Wiring</p>

---

## Функции

Compressed air supply min.	5,5 бар
Compressed air supply max.	6 бар
Номинальное рабочее напряжение	230 В, 1~, 50 Гц/60 Гц
Управляющее напряжение (DC)	24 В
Потребляемая мощность (ок.)	1 кВт
Тактовое время	11 с
Проводов в час ок.	320
Занимаемая площадь	Ширина: 2.170 мм Высота: 1.870 мм Глубина: 1.080 мм
Код ТНВЭД	84633000
ETIM 8	EC000000
ECLASS 8.0	18129090
Описание продукта	Wire Terminal WT L5 T fully automated wire processing machine (wire feeder unit for the Wire Handling System)