

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.080**

**Ручной гидравлический пресс в наборе M16 - M40**

Состояние: 10.02.2026 (Источник: [rittal.com/kz-ru](http://rittal.com/kz-ru))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AS 4055.080 - Ручной гидравлический пресс в наборе M16 - M40

Manual hydraulic punch in a practical set with hole punches for sheet steel. Maximum machinable material thickness 2 or 3 mm.

## ФУНКЦИИ

Арт. №	AS 4055.080
Исполнение	с повернутой на 90° и вращаемой на 360° цилиндрической головкой
Описание продукта	
Преимущества	Увеличение срока службы инструмента благодаря встроенному клапану избыточного давления
Комплект поставки	Ручной гидравлический пресс 5 штампов с тройным сегментированием Гидравлический винт Ø 19 мм Гидравлический винт Ø 9,5/19 мм Сверло черновое HSS Ø 10 мм Набор распорных втулок (3-компонентный) Пластиковый футляр
Обрабатываемый материал	Листовая сталь
Макс. толщина обрабатываемой листовой стали	2 мм 2 мм 2 мм 3 мм 3 мм
Ø выреза	16,2 мм 20,4 мм 25,4 мм 32,5 мм 40,5 мм

# ФУНКЦИИ

Для резьбы	M16
	M20
	M25
	M32
	M40
Упаковка	1 шт.
Вес нетто	4.1
Gross weight	4.16
Код ТНВЭД	84678900
EAN	4028177807952
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046