



Rittal – The System.

Faster – better – everywhere.



VX 8617.120

Системные шасси 23 x 64 мм


Состояние: 29.01.2026 (Источник: rittal.com/kz-ru)



FRIEDHELM LOH GROUP

VX 8617.120 - Системные шасси 23 x 64 мм для VX, VX IT, VX SE, AX из пластика

Для гибкого и индивидуального внутреннего монтажа.



ФУНКЦИИ

Арт. №	VX 8617.120
Описание продукта	Для гибкого и индивидуального внутреннего монтажа.
Преимущества	Просто навешиваются в системную перфорацию и закрепляются Системная перфорация со всех четырех сторон С перфорацией сверху и снизу для закладных гаек для крепления собственных компонентов метрическими винтами
Материал	Листовая сталь
Поверхность	Оцинкованная
Комплект поставки	Вкл. крепежный материал
VX installation options	In enclosure depth 500 mm, on the inner mounting level
VX SE installation options	In enclosure depth 500 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility
AX installation options	In enclosure width/height 500 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
AX stainless steel installation options	In enclosure width/height 500 mm, in conjunction with the base configuration rail

ФУНКЦИИ

Installation options, AX plastic	In enclosure width 500 mm, in conjunction with universal bracket
CX installation options	In the pedestal, in the enclosure depth, 500 mm
VX base/plinth installation options	In base/plinth width/depth 600 mm for mounting on the base/plinth corner pieces
Подходит для	Тип корпуса: VX VX IT VX SE AX AX пластик Suitable for width or height or depth: 500 мм
Подходит для	Система цоколей VX
Упаковка	4 шт.
Вес нетто	1.6
Gross weight	1.98
Код ТНВЭД	73269098
EAN	4028177829121
ETIM 9	EC002620
ECLASS 8.0	27189234