


Rittal – The System.

Faster – better – everywhere.



RX 9360.230

RiLineX connection adaptor

Состояние: 25.05.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.230 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support through-wiring. Mounted by simply snapping onto the RiLineX board. The supply leads and adaptors are screw-fastened onto the board together. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.



Функции

Арт. №	RX 9360.230
Преимущества	Mounting on the busbar system and cable connection with just one screw
Материал	Полиамид (PA 6) Негорючесть согласно UL 94
Цвет	RAL 9005
Номинальный ток (макс.)	375 A
Номинальный ток макс.	630 A
Rated current of round conductor	630 A
Rated current of round conductor (UL)	600 A

Функции

Rated current of laminated copper bar	790 A
Rated current of laminated copper bar (UL)	760 A
Electrical ratings UL (SCCR)	27,5 kA - 600 V, RMS, unprotected 100 kA - 600 V, circuit breaker max. 400 A, DIVQ/7 100 kA - 600 V, Fuse Class L max. 1200 A, JDDZ/7
Отвод проводов	сверху/снизу
Для шинных систем с межцентровым расстоянием	60 mm
Количество полюсов	3-пол.
Подходит для шинной системы	RiLineX RiLine60
Размер	Ширина: 126,8 мм Высота: 239,4 мм Глубина: 104,6 мм
Подключение проводов	95 - 240 мм ²
Клемма для гибких медных шин (Ш x В)	24 x 20 мм
Rated voltage	1 000 V AC 1 500 V DC 600 V AC (UL) 600 V DC (UL)
Категория перенапряжения	4
Степень загрязнения	3
Стандарты	IEC/EN 61439-1 UL 508
Номинальное импульсное напряжение U _{imp}	12 кВ
Номинальное напряжение изоляции U _i	1 000 В
Тепловыделение макс.	20 Вт

Функции

Степень защиты IP согл. МЭК 60 529	IP 2XB
Maximum operating air humidity	90 %
Диапазон рабочих температур	-5 °C...55 °C
Диапазон температур хранения	-25 °C...75 °C
Влажность воздуха (без конденсата)	10...90 %
Упаковка	1 шт.
Вес нетто	1,5 kg
Gross weight	1,62 kg
PCF per pack (cradle-to-gate)	8,65
Код ТНВЭД	85369010
ETIM 9	EC001531
Описание продукта	RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support through-wiring. Mounted by simply snapping onto the RiLineX board. The supply leads and adaptors are screw-fastened onto the board together. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.

Одобрения

Одобрения	UL + C-UL (listed)
Объяснения	Декларация о соответствии PCF-declaration