

Rittal – The System.

Faster – better – everywhere.



AE 1005.600

Compact enclosures AE

State: 2026.6.6 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1005.600 - Compact enclosures AE Stainless steel

Compact enclosure AE in stainless steel including mounting plate.

Features

Model No.	AE 1005.600
Material	Enclosure: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Sheet steel Stainless steel 1.4301 (AISI 304)
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure with door(s) Mounting plate Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 300 mm Height: 380 mm Depth: 210 mm
Dimensions mounting plate (W x H)	275 mm x 334 mm
Number of doors	1
Number of locks	1
Lock	Lock version: Cam Number of locks: 1 Lock insert: 3 mm double-bit Material lock: Die-cast zinc, nickel-plated
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).

Features

Net weight	7.7 kg
Gross weight	7.88 kg
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	AE Compact enclosure, WHD: 300x380x210 mm, Stainless steel 1.4301, with mounting plate, single-door, with one cam lock

Approvals

Approvals	DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Stainless steel enclosure (compact enclosure);
protection category IP 66

Enclosure:

Made from 1.4301 (V2A) 1.25 or 1.5 mm stainless steel.
Folded and welded from a single piece with protection
channel around the door opening.

Doors:

1.5 or 2 mm 1.4301 stainless steel, flush-mounted, with
foamed-in seal, concealed hinges, 130° opening angle as
per VDI, cam lock with double-bit insert as per DIN
43668.

Mounting plate:

2 - 3 mm sheet steel with system punchings,
depth-adjustable stud mountings, zinc-plated.

Accessories:

Locking systems, earthing straps, wiring plan pockets,
door stay,
heat exchangers, fan-and-filter units, heaters, viewing
window, panels

Surface finish:

Brushed

Dimensions (W x H x D): 300 x 380 x 210 mm