
Rittal – The System.

Faster – better – everywhere.



# SZ 2388.050

# Rail

State: 2026.10.31 (Source: www.rittal.com/lt-en)


ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SZ 2388.050 - Rail for EMC shielding bracket and strain relief

Combined rail for strain relief and EMC contacting of inserted cables.





## Features

| | |
|---|---|
| Model No. | SZ 2388.050 |
| Design | C rail to accommodate cable clamps<br>T-head cut-outs on a 40 mm pitch pattern for cable clamping using cable ties |
| Product description | Combined rail for strain relief and EMC contacting of inserted cables. |
| Benefits | Additional contacting on the left or right of the rail via existing holes (9 mm diameter)<br>Prepared for tool-free mounting of EMC shielding brackets |
| Material | Extruded aluminium section |
| Surface finish | Chromium-free passivated |
| Supply includes | 1 rail<br>2 retaining brackets<br>Assembly parts |
| Length | 953 mm |
| Installation options | on the horizontal/vertical enclosure section<br>may also be fitted without a retaining bracket on a mounting plate |
| To fit | Enclosure type: VX<br>TS<br>Width: = 1,000 mm |
| Packs of | 1 pc(s). |

© Rittal 2026

# Features

| | |
|---|---|
| Net weight | 0.76 kg |
| Gross weight | 0.84 kg |
| Customs tariff number | 76042990 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | SZ Rail, for EMC rail and stain relief, for W: 1000 mm |