

# Rittal – The System.

Faster – better – everywhere.



## SZ 2411.811

### Cable gland, brass

State: 2026.2.3 (Source: [ittal.com/lt-en](https://ittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.811 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

## Features

Model No.	SZ 2411.811
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
IP protection category to IEC 60 529	IP 68 (5 bar, 30 min)
Dimensions	Height: 28 mm
Thread	M16 x 1.5
Thread length	7 mm
Min. cable diameter	5 mm
Max. cable diameter	10 mm
Operating temperature range	-40 °C...100 °C
torque	9 Nm
Width across flats	20 mm
Dimensions	Thread: M16 x 1.5 Thread length: 7 mm
Type rating to UL 50E	Type 4X
Packs of	15 pc(s).
Net weight	0.3
Gross weight	0.451

# Features

---

Customs tariff number 74198090

EAN 4028177810082

ETIM 9 EC000441

ETIM 8 EC000441

ECLASS 8.0 27149109

# Approvals

---

Approvals UR + C-UR (recognized)  
VDE

Explanations Declaration of conformity  
Declaration of conformity UK