Rittal – The System.

Faster – better – everywhere.



# SZ 2411.841

# Cable gland, brass

State: 2026.11.15 (Source: www.rittal.com/lt-en)

# SZ 2411.841 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

## Features

| | |
|---|---|
| Model No. | SZ 2411.841 |
| Benefits | Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage.<br>Clamping membranes for even tightening and strain relief to protect the cables |
| Material | Brass<br>Seal: CR/NBR |
| Surface finish | Nickel-plated |
| IP protection category to IEC 60 529 | IP 68 (5 bar, 30 min) |
| Dimensions | Height: 36 mm |
| Thread | M32 x 1.5 |
| Thread length | 8 mm |
| Min. cable diameter | 15 mm |
| Max. cable diameter | 21 mm |
| Operating temperature range | -40 °C...100 °C |
| torque | 15 Nm |
| Width across flats | 34 mm |
| Dimensions | Thread: M32 x 1.5<br>Thread length: 8 mm |
| Type rating to 508A | Type 1<br>Type 4<br>Type 4X<br>Type 12<br>Type 13 |
| Packs of | 5 pc(s). |

© Rittal 2026

# Features

| | |
|---|---|
| Net weight | 0.475 kg |
| Gross weight | 0.495 kg |
| Customs tariff number | 74198090 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |
| Product description | SZ Cable gland, brass, size: M32x1,5, for cables ø 15-21 mm |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed)<br>VDE |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |