


Rittal – The System.

Faster – better – everywhere.



SK 3108.100

Enclosure internal fan

State: 2025.8.24 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3108.100 - Enclosure internal fan

To prevent hot-spots inside the enclosure and support the air routing of active enclosure climate control components.



Features

| | |
|-------------------------|--|
| Model No. | SK 3108.100 |
| Product description | To prevent hot-spots and support the air routing of active enclosure climate control components. Adjustable in two axes. Attached to the frame section. Several fans may be cascaded using the quick-release clamping strip. |
| Supply includes | Complete unit with axial fan ready for connection Snap-on pivot device Assembly parts |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Power consumption Pel | At 50 Hz: 19 W At 60 Hz: 18 W |
| Rated current max. | At 50 Hz: 0.12 A At 60 Hz: 0.11 A |
| Packs of | 1 pc(s). |
| Net weight | 0.94 |
| Gross weight | 1.126 |
| Customs tariff number | 84145915 |
| EAN | 4028177220485 |

Features

| | |
|------------|----------|
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|