


# Rittal – The System.

Faster – better – everywhere.



## SM 2384.010

## Switch housings

State: 2026.2.7 (Source: [ittal.com/lt-en](https://ittal.com/lt-en))



# SM 2384.010 - Switch housings Stainless steel

Switch housing made from stainless steel 1.4301 (AISI 304) with switch cut-outs, diameter: 22.5 mm. Protection category IP 66.

## Features

Model No.	SM 2384.010
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal
Surface finish	Enclosure and cover: Brushed, grain 240
Supply includes	Enclosure with cover Quick-release fastener including plastic bushes
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 100 mm Height: 100 mm Depth: 90 mm
Material thickness - cover	1.25 mm
Material thickness - enclosure	1.25 mm
Pitch pattern	60 mm
Cut-outs (quantity x diameter)	1 x 22.5 mm
Lock	Lock version: Quick-release fastener including plastic bushes Number of locks: 2
Cable entry (quantity x diameter)	1
No. of metric knockouts	1
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).
Net weight	0.68

## Features

---

Gross weight	0.72
Customs tariff number	94039910
EAN	4028177529403
ETIM 9	EC000261
ETIM 8	EC000261
ECCLASS 8.0	27180101

## Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---