

Rittal – The System.

Faster – better – everywhere.



SK 3303.100

Wall-mounted cooling units

State: 2026.7.6 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3303.100 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.



Features

Model No.	SK 3303.100
Material	Sheet steel
Supply includes	Fully wired ready for connection Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 500 W Cooling output L35 L35/60 Hz: 610 W Cooling output L35 L50/50 Hz: 280 W Cooling output L35 L50/60 Hz: 350 W
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 2.6 A At 60 Hz: 2.6 A
Start-up current max.	At 50 Hz: 5.1 A At 60 Hz: 6.4 A
Air throughput (unimpeded air flow)	External circuit: 345 m ³ /h Internal circuit: 310 m ³ /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.4
Design	wall-mounted

Features

Dimensions	Width: 280 mm Height: 550 mm Depth: 210 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.17 kg
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	20 °C...55 °C
Setting range	30 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 36 W Power consumption L35 L35/60 Hz: 380 W Power consumption L35 L50/50 Hz: 420 W Power consumption L35 L50/60 Hz: 390 W
Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Packs of	1 pc(s).
Net weight	17 kg
Gross weight	17.7 kg
Customs tariff number	84158200
ECLASS 8.0	27180704
Product description	SK RTT Cooling unit, wall-mounted, 500 W, 230 V, basic controller

Approvals

Approvals	UL + C-UL (listed) UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Wall-mounted cooling unit Rittal TopTherm PLUS
with RiNano coating

Useful cooling output to DIN 3168 L35 L35 500/610 W

Rated operating voltage 230 V, 50/60 Hz

Power consumption Pel to DIN 3168 L35 L35 360/380 W

Dimensions W x H x D [mm] 280 x 550 x 200

Refrigerant R 134 a

Temperature range 20°C to 55°C (Setting range +30°C to +55°C)

Temperature control and monitoring via basic
controller with floating fault signal contact
and connection for door operated switch

Factory setting 35°C

Connection by pluggable terminal strip

Protection category to EN 60 529/10.91

External circuit IP 34/Internal circuit IP 54

Weight 17 kg

Colour RAL 7035