

# Rittal – The System.

Faster – better – everywhere.



## SK 3127.115

# TopTherm air-air heat exchanger

State: 2026.5.13 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3127.115 - TopTherm air-air heat exchanger wall-mounted with controller

Fully wired wall-mounted heat exchanger unit with controller and digital temperature display.

## Features

|                                     |  |
|-------------------------------------|--|
| Model No.                           | SK 3127.115  |
| Design                              | wall-mounted   |
| Product description                 | Air/air heat exchangers are particularly well-suited to aggressive ambient conditions, because the internal and external air circuits are completely separate from one another.                                  |
| Colour                              | RAL 7035   |
| Supply includes                     | Complete unit ready for connection<br>Plug-in terminal strip<br>Floating fault signal contact in case of overtemperature<br>Drilling template<br>Assembly parts  |
| Specific thermal output             | 30 W/K   |
| Air throughput (unimpeded air flow) | External circuit with 50 Hz: 480 m <sup>3</sup> /h<br>External circuit with 60 Hz: 525 m <sup>3</sup> /h<br>Internal circuit at 50 Hz: 480 m <sup>3</sup> /h<br>Internal circuit at 60 Hz: 525 m <sup>3</sup> /h |
| Rated operating voltage             | 115 V, 1~, 50 Hz/60 Hz   |
| Rated current max.                  | At 50 Hz: 1.1 A<br>At 60 Hz: 1.4 A   |
| Dimensions                          | Width: 400 mm<br>Height: 950 mm<br>Depth: 205 mm   |
| Pre-fuse                            | Miniature circuit-breaker/fuse: 2 A  |
| Temperature control                 | Electronic control with digital display (factory setting +35 °C)   |
| Operating temperature range         | -5 °C...55 °C  |

## Features

|                                     |  |
|-------------------------------------|--|
| IP protection category to IEC 60529 | Internal circuit IP 54<br>External circuit IP 34   |
| Packs of                            | 1 pc(s).   |
| Net weight                          | 18.5 kg  |
| Gross weight                        | 19.051 kg  |
| Customs tariff number               | 84158300   |
| ETIM 9                              | EC002514   |
| ETIM 8                              | EC002514   |
| ECLASS 8.0                          | 27180711   |
| Product description                 | SK TopTherm air/air heat exchanger, wall-mounted, 30 W/K, 115V, 50/60Hz, WHD: 400 x 950 x 205 mm |

## Approvals

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |