


# Rittal – The System.

Faster – better – everywhere.



## SK 3189.640

## Wall-mounted cooling unit Blue e+

State: 2025.8.28 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3189.640 - Wall-mounted cooling unit Blue e+ 1.6 - 5.5 kW

Energy-efficient Blue e+ wall-mounted cooling units in output categories 1600 W to 5500 W. Average energy savings of 75% can be achieved with speed-regulated components and heat pipe technology. Available in sheet steel and stainless steel versions.



## Features

|                      |   |
|----------------------|---|
| Model No.            | SK 3189.640   |
| Design               | wall-mounted  |
| Benefits             | Average 75% energy savings thanks to speed-regulated components and heat pipe technology<br>Suitable for international use due to a unique multi-voltage capability<br>Longer service life of the components inside the enclosure and the cooling unit due to component-friendly cooling<br>Intuitive operation due to touch display and intelligent interfaces |
| Product modification | The cover for the connection box to protect the electrical connection to the cooling unit has not been included with the supply since the start of 2024. Covers 3355.200 and 3355.210 can be ordered as optional accessories.   |
| Material             | Stainless steel 1.4301 (AISI 304)   |
| Colour               | RAL 9007  |
| Supply includes      | Condenser with hydrophobic RiNano coating<br>Integral electric condensate evaporation<br>Assembly parts<br>Fully wired ready for connection (plug-in terminal strip)  |

# Features

|  |  |
|--|--|
| Options  | For remote monitoring and networking of cooling units and chillers in the Blue e+ generation, please use the IoT interface (Model No. 3124.300). Increase machine availability and process reliability with remote monitoring of device data, statuses and system messages.                                  |
| Total cooling output to DIN EN 14511             | Cooling output L35 L35/50 Hz: 5.5 kW<br>Cooling output L35 L35/60 Hz: 5.5 kW<br>Cooling output L35 L50/50 Hz: 3.95 kW<br>Cooling output L35 L50/60 Hz: 3.95 kW   |
| Rated operating voltage                          | 380 V - 480 V, 3~, 50 Hz/60 Hz   |
| Note   | Please observe the mounting instructions.<br>By downloading the software, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these licence conditions.<br>Only suitable for use in semi-outdoor areas (see instructions for description) |
| Note on Model No.                                | Tolerance: 380 V -10% (342 V) and 480 V +5% (509 V)<br>Full installation not possible  |
| Rated power input                                | 2.35 kW  |
| Air throughput (unimpeded air flow)              | External circuit: 2,300 m³/h<br>Internal circuit: 2,300 m³/h   |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35   | Refrigeration factor L35 L35 (EER) 50 Hz: 2.5<br>Refrigeration factor L35 L35 (EER) 60 Hz: 2.5   |
| Seasonal energy efficiency ratio (SEER) 50/60 Hz | 5.6  |
| Design   | wall-mounted   |
| Dimensions                                       | Width: 450 mm<br>Height: 1,600 mm<br>Depth: 393 mm   |
| Required mounting cut-out                        | Cut-out width: 433 mm<br>Cut-out height: 1,579 mm  |
| Protection category to IEC 60 529                | Internal circuit IP 55   |
| Protection category NEMA                         | UL Type 12<br>UL Type 3R   |

# Features

|   |  |
|---|--|
| Refrigerant/cooling medium                                  | Refrigerant: R-513A<br>Quantity: 1.8 kg<br>Global Warming Potential (GWP): 631<br>CO2 equivalent (CO2e): 1.14 t  |
| Temperature control   | e+ controller (factory setting +35 °C)   |
| Operating temperature range                                 | -20 °C...60 °C   |
| Storage temperature range                                   | -40 °C...70 °C   |
| Operating temperature range of refrigerant circuit (active) | 3 °C...60 °C   |
| Heat pipe operating temperature range                       | -20 °C...45 °C   |
| Setting range   | 20 °C...50 °C  |
| Power consumption Pel                                       | Power consumption L35 L35/50 Hz: 2.2 kW<br>Power consumption L35 L35/60 Hz: 2.2 kW<br>Power consumption L35 L50/50 Hz: 2.2 kW<br>Power consumption L35 L50/60 Hz: 2.2 kW |
| Permissible operating pressure (p. max.)                    | 24 bar   |
| Packs of  | 1 pc(s).   |
| Net weight  | 71.2   |
| Gross weight  | 91   |
| Customs tariff number                                       | 84158200   |
| EAN   | 4028177934641  |
| ETIM 9  | EC000855   |
| ETIM 8  | EC000855   |
| ECLASS 8.0  | 27180704   |

## Approvals

# Approvals

|              |   |
|--------------|---|
| Approvals    | IEC CB<br>30 - KC Korea<br>UL + C-UL (listed)             |
| Certificates | EAC   |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |