

# Rittal – The System.

Faster – better – everywhere.



## SK 3329.610

# TopTherm wall-mounted cooling unit Blue e

State: 2026.5.2 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3329.610 - TopTherm wall-mounted cooling unit Blue e 0.3 - 4 kW

Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W). Available in the special formats "horizontal" and "flat".



## Features

|   |   |
|---|---|
| Model No.                               | SK 3329.610   |
| Design                                  | wall-mounted  |
| Product description                     | Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W).                             |
| Benefits                                | May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller   |
| Material                                | Stainless steel 1.4301 (AISI 304)   |
| Colour                                  | RAL 9007  |
| Supply includes                         | Condenser with hydrophobic RiNano coating<br>Fully wired ready for connection (plug-in terminal strip)<br>Drilling template<br>Assembly parts<br>Integral electric condensate evaporation |
| Total cooling output to<br>DIN EN 14511 | Cooling output L35 L35/50 Hz: 2.55 kW<br>Cooling output L35 L35/60 Hz: 2.71 kW<br>Cooling output L35 L50/50 Hz: 1.8 kW<br>Cooling output L35 L50/60 Hz: 1.8 kW                            |

# Features

|  |   |
|--|---|
| Rated operating voltage                        | 115 V, 1~, 50 Hz/60 Hz  |
| Rated current max.                             | At 50 Hz: 17 A<br>At 60 Hz: 22 A  |
| Start-up current max.                          | At 50 Hz: 44 A<br>At 60 Hz: 42 A  |
| Air throughput (unimpeded air flow)            | External circuit: 710 m <sup>3</sup> /h<br>Internal circuit: 640 m <sup>3</sup> /h  |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 2.11<br>Refrigeration factor L35 L35 (EER) 60 Hz: 2.01  |
| Design   | wall-mounted  |
| Dimensions                                     | Width: 400 mm<br>Height: 1,580 mm<br>Depth: 295 mm  |
| Protection category to IEC 60 529              | External circuit IP 34<br>Internal circuit IP 54  |
| Protection category NEMA                       | UL Type 12  |
| Refrigerant/cooling medium                     | Refrigerant: R134a<br>Quantity: 0.95 kg<br>Global Warming Potential (GWP): 1,430<br>CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 1.36 t                                  |
| Temperature control                            | e-Comfort controller (factory setting +35 °C)   |
| Operating temperature range                    | 10 °C...55 °C   |
| Storage temperature range                      | -40 °C...70 °C  |
| Setting range                                  | 20 °C...55 °C   |
| Power consumption Pel                          | Power consumption L35 L35/50 Hz: 1.21 kW<br>Power consumption L35 L35/60 Hz: 1.05 kW<br>Power consumption L35 L50/50 Hz: 1.5 kW<br>Power consumption L35 L50/60 Hz: 1.73 kW |
| Permissible operating pressure (p. max.)       | 28 bar  |
| Note on Model No.                              | Extended delivery times.  |
| Pre-fuse                                       | Transformer circuit-breaker: 18...25 A  |

# Features

---

|                       |  |
|-----------------------|--|
| Packs of              | 1 pc(s).   |
| Net weight            | 76 kg  |
| Gross weight          | 76 kg  |
| Customs tariff number | 84158200   |
| ETIM 9                | EC000855   |
| ETIM 8                | EC000855   |
| ECLASS 8.0            | 27180704   |
| Product description   | SK Cooling unit Blue e, wall-mounted, 2.5 kW, 115 V, 1~, 50/60 Hz, stainless steel, WHD: 400 x 1580 x 295 mm |

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | UL + C-UL (listed)<br>UL + C-UL - FTTA<br>UR + C-UR (recognized)   |
| Explanations | FCC<br>Declaration of conformity<br>Declaration of conformity - F-gas regulation<br>Declaration of conformity UK |