
Rittal – The System.

Faster – better – everywhere.





SK 3212.230 Air-water heat exchangers

State: 2025.10.17 (Source: rittal.com/lt-en)



SK 3212.230 - Air-water heat exchangers wall-mounted

Output classes 375 – 5,000 W. For use in tough environments. Convenient mounting options and flexible water connection options. External mounting or full internal mounting possible.

Features

| Model No. | SK 3212.230 | |
|--|---|--|
| Design | wall-mounted Water-carrying parts, copper/brass (Cu/CuZn) | |
| Product description | For use in harsh environments and temperature ranges up to +70 °C. User-friendly assembly plus flexible water connection options External mounting or full internal mounting are supported. | |
| Colour | RAL 7035 | |
| Supply includes | Fully wired ready for connection Drilling template Sealing and assembly parts | |
| Total cooling output | L 35 W 10 at 200 l/h: 0.3 kW | |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz | |
| Power consumption Pel | At 50 Hz: 23 W At 60 Hz: 27 W | |
| Rated current max. | At 50 Hz: 0.11 A At 60 Hz: 0.13 A | |
| Permissible operating pressure (p. max.) | 1 - 10 bar | |
| Duty cycle | 100 % | |
| Cooling medium | Water (see Internet for specifications) | |
| Water inlet temperature | 1 °C30 °C | |
| Water connections | 3%" connector sleeve | |
| Operating temperature range | 1 °C70 °C | |
| Note | Integral non-return valve for version with e-Comfort controller | |

© Rittal 2025 2

Features

| Dimensions | Width: 150 mm |
|-----------------------------------|-------------------------------------|
| | Height: 300 mm |
| | Depth: 85 mm |
| Pre-fuse | Miniature circuit-breaker/fuse: 2 A |
| Setting range | 20 °C55 °C |
| Protection category to IEC 60 529 | IP 55 |
| Packs of | 1 pc(s). |
| Net weight | 3.227 |
| Gross weight | 3.427 |
| Customs tariff number | 84158300 |
| EAN | 4028177430938 |
| ETIM 9 | EC002515 |
| ETIM 8 | EC002515 |
| ECLASS 8.0 | 27180712 |
| | |

Approvals

| Explanations | Declaration of conformity | |
|--------------|---------------------------|--|
|--------------|---------------------------|--|

© Rittal 2025 3

Tender text

Wall-mounted air/water heat exchanger For use in tough environments. Flexible water connection options.

Total cooling output L 35 W 10, 200l/h: 0.3 kW Rated operating voltage: 230 V, 50/60 Hz Refrigerant: Water (see specifications)

Water-carrying parts: Cu/CuZn

Dimensions [W x H x D]: 150 x 300 x 85 mm Ambient temperature range: 1°C to 70°C Water inlet temperature range: 1°C to 30°C Type of connection: Plug-in terminal strip Protection category to IEC 60 529: IP 55

Weight: 3.2 kg Colour: RAL 7035

© Rittal 2025 4