

Rittal – The System.

Faster – better – everywhere.



SK 3385.500

TopTherm Blue e roof-mounted cooling unit

State: 2025.5.3 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3385.500 - TopTherm Blue e roof-mounted cooling unit

Total cooling output 0.50 - 4.00 kW

Energy-efficient Blue e roof-mounted cooling units in output categories from 500 W to 4,000 W with e-Comfort controller integrated as standard and electrical condensate evaporation.



Features

| | |
|---------------------|---|
| Model No. | SK 3385.500 |
| Design | roof-mounted |
| Product description | Energy-efficient Blue e roof-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. |
| Benefits | May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Condenser with hydrophobic RiNano coating Integral electric condensate evaporation Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts |

Features

| | |
|--|---|
| Total cooling output to DIN EN 14511 | Cooling output L35 L35/50 Hz: 2 kW Cooling output L35 L35/60 Hz: 2.14 kW Cooling output L35 L50/50 Hz: 1.58 kW Cooling output L35 L50/60 Hz: 1.51 kW |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Note | The roof-mounted cooling unit 3273.500 is also suitable for office applications, thanks to its low noise level. |
| Rated current max. | At 50 Hz: 6.5 A At 60 Hz: 7.9 A |
| Start-up current max. | At 50 Hz: 19.7 A At 60 Hz: 17.9 A |
| Air throughput (unimpeded air flow) | External circuit: 1,760 m³/h Internal circuit: 470 m³/h |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 1.96 Refrigeration factor L35 L35 (EER) 60 Hz: 1.69 |
| Design | roof-mounted |
| Dimensions | Width: 597 mm Height: 417 mm Depth: 475 mm |
| Protection category to IEC 60 529 | External circuit IP 34 Internal circuit IP 54 |
| Refrigerant/cooling medium | Refrigerant: R-513A Quantity: 0.9 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.57 t |
| Type of electrical connection | Plug-in terminal strip |
| Duty cycle | 100 % |
| Temperature control | e-Comfort controller (factory setting +35 °C) |
| Operating temperature range | 10 °C...55 °C |
| Operating temperature max @60 Hz | 53 °C |
| Storage temperature range | -40 °C...70 °C |

Features

| | |
|--|--|
| Setting range | 20 °C...53 °C |
| Power consumption Pel | Power consumption L35 L35/50 Hz: 1.02 kW Power consumption L35 L35/60 Hz: 1.27 kW Power consumption L35 L50/50 Hz: 1.15 kW Power consumption L35 L50/60 Hz: 1.29 kW |
| Permissible operating pressure (p. max.) | 28 bar |
| Pre-fuse | Miniature circuit-breaker/fuse: 10 A |
| Packs of | 1 pc(s). |
| Net weight | 50 |
| Gross weight | 51.7 |
| Customs tariff number | 84158200 |
| EAN | 4028177323278 |
| ETIM 9 | EC000855 |
| ETIM 8 | EC000855 |
| ECLASS 8.0 | 27180704 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) UL + C-UL - FTТА |
| Certificates | EAC |
| Explanations | Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK |